

# Ultrapolymem® PF-PP

*Membrane filter for purification of solvents, alcohols, chemicals, gases*

## Product Description

The Ultrapolymem PF-PP filter is constructed of 100% polypropylene, including the pleated membrane media, support cage and end caps. It provides maximum durability against chemicals in critical processes.

With similar performance, durability, and chemical compatibility, Ultrapolymem PF-PP filters offer a cost-effective alternative to PTFE membrane filters.

The polypropylene filter media is inherently hydrophobic, with a highly porous membrane structure. It provides consistent performance throughout its entire service life. PF-PP filters are especially suitable for a wide range of liquids and gases.

## Features

All components meet FDA requirements for contact with food in accordance with CFR (Code of Federal Regulations) Title 21. Ultrapolymem PF-PP filter elements have passed the toxicological tests according to USP XX Class VI for plastics. In particular, requirements of the chemical, biological, cosmetic, electronic and pharmaceutical industries are met.


The membrane is manufactured in accordance with cGMP\* requirements, is non-fiber-releasing, and is thermally-welded without the use of binders or other chemical additives.

## Applications

- Acids
- Bases
- Alcohols
- Solvents
- Etchants
- Photoresists
- Compressed Air
- Technical Gases



The Ultrapolymem PF-PP polypropylene membrane filter is a cost-effective alternative to PTFE



Ultrapolymem PF-PP membrane as seen under the scanning electron microscope

\* cGMP: current Good Manufacturing Practices

Features	Benefits
All-polypropylene construction	Strong durability against chemicals, permits use in broad range of fluids and applications
Absolute ratings of 0.04, 0.1 and 0.2 $\mu\text{m}$	Precise particle retention at rated level, 0.2 $\mu\text{m}$ meets bacterial validation acc. to HIMA/ASTM standards
Unique polypropylene membrane	High flow rates, long service life, cost effective alternative to PTFE membranes
Inherently hydrophobic	Natural barrier to water without the use of additives or surface modifying agents which can leach or wash out
Rugged thermal bonded construction	Reliable integrity under severe process conditions withstands multiple sterilizations
Contains no binders or adhesives	Wide solvent compatibility, extremely low extractables
Fully integrity testable	Assurance of product integrity and effectiveness in operation
Biologically inert and non-toxic	Meets FDA requirements for food contact, passed UPS Class VI biological tests for plastics
100% integrity tested by factory	Assured product reliability and consistency

Dimensions	
Diameter:	2.75"
Length:	5", 10", 20", 30" or 40"

Integrity testing	
Wetting agent Isopropylalcohol (IPA)	
Pore size	Bubble point
0.04 $\mu\text{m}$	$\geq 26$ psig
0.1 $\mu\text{m}$	$\geq 22$ psig
0.2 $\mu\text{m}$	$\geq 9$ psig

Maximum differential pressure	
Operating temp.	Differential pressure
100°F	80 psid
150°F	60 psid
180°F	30 psid

Materials	
Membrane:	Polypropylene
Upstream support:	Polypropylene
Downstream support:	Polypropylene
Outer guard:	Polypropylene
Endcaps:	Polypropylene
O-Ring:	Silicone, Buna N, EPDM or Viton®

\*Viton is a registered trademark of E.I. du Pont de Nemours and Company


Bacterial retention
HIMA challenge per ASTM 0.2 $\mu\text{m}$
Pseudomonas diminuta

Filtration surface
6.5 ft <sup>2</sup> for 10" element


Sterilization
<b>In-line sterilization with slow speed saturated steam</b> 250°F - 275°F for 30-60 minutes
<b>Autoclave</b> 260°F for 30-60 minutes
Ultrapolymem® PF-PP filter elements are capable of repeated sterilization cycles without loss of integrity

Absolute retention rate
0.04 $\mu\text{m}$ , 0.1 $\mu\text{m}$ , 0.2 $\mu\text{m}$

PF-PP Pressure Drop per Ten Inch Equivalent (TIE) — Water



PF-PP Pressure Drop per Ten Inch Equivalent (TIE) — Air



Donaldson Company, Inc.  
Process Filtration  
P.O. Box 1299  
Minneapolis, MN  
55440-1299 U.S.A.  
Tel 800.543.3634 (USA)  
Tel 800.343.3639 (within Mexico)  
processfilters@mail.donaldson.com  
www.donaldson.com

Information in this document is subject to change without notice.  
© 2007 Donaldson Company, Inc.  
Printed in U.S.A. on recycled paper